



www.amiad.com

Arkal ¾" Filter


Catalog No. 012000-*****


Features

- "All plastic", with two 3/4" male connections.
- The filter element consists of grooved discs, mounted on a spine, forming a cylindrical filter element. The discs are compressed together by a spring located at the bottom of the filter cover.
- Screw-on filter cover.
- Filter discs available in various filtration grades.
- Resistant to chemicals and liquid fertilizers.

Technical Data

| | ¾" BSPT (male) | ³ ⁄ ₄ " BSPT (male) |
|--------------------------------|---------------------------------|--|
| Inlet/Outlet diameter | 20 mm - nominal diameter | |
| | 26.7 mm - pipe diameter (O. D.) | |
| Maximum pressure | 10 bar | 145 psi |
| Maximum flow rate | 4 m ³ /h (1.1 l/sec) | 18 gpm |
| Total filtration area | 160 cm ² | 24 ¹³ / ₁₆ in ² |
| Total filtration volume | 95 cm ³ | 5 ¹³ / ₁₆ in ³ |
| Filter length L | 144 mm | 5 11/16" |
| Filter width W | 74 mm | 2 29/32" |
| Distance between connections A | 150 mm | 5 29/32" |
| Weight | 0.37 Kg | 0.8 lbs |
| Maximum temperature | 60º C | 140º F |
| рН | 3-12 | 3-12 |






Filtration Grades

| Blue | (400 micron / 40 mesh) |
|--------|-------------------------|
| Yellow | (200 micron / 80 mesh) |
| Red | (130 micron / 120 mesh) |
| Black | (100 micron / 140 mesh) |

Headloss Chart FLOW RATE









www.amiad.com

Installation

- 1. Use Teflon tape on filter threads.
- 2. Ensure correct inlet/outlet direction.
- 3. When connecting filter to pipe do not over tighten.

Dismantling

- 1. Make certain that no pressure remains in pipeline.
- 2. Unscrew cover at bottom of filter.
- 3. Pull out entire filter element.
- Move tightening ring to end of spine and flush discs with pressurized water.

Assembly

- 1. Verify that spring is in place inside the filter cover.
- 2. Assemble in reverse order.
- 3. Tighten filter cover securely. Do not over tighten.

Winterization


Drain all the water from filter to avoid cracking due to freezing.

Part List - ¾" Filter

| No. | Cat. No. | Description | Materials |
|-----|---------------|------------------|-----------|
| 1 | 710101-000844 | Filter body | PBT |
| 2 | 770101-000009 | Cover o-ring | NR |
| | 770101-000003 | Cover o-ring | VITON |
| 3 | 710101-000129 | Stopper ring | PP |
| 4 | 710101-000846 | Spine tightening | PP |
| | | ring | |
| 5 | 710101-000851 | Filter spine | PP |
| 6 | 700101-***** | Disc set | PP / PE |
| 7 | 760107-000001 | Compression | SS |
| | | spring | |
| 8 | 710103-001317 | Filter cover | PBT |
| 9 | 700101-***** | Filter element | PP / PE |

Materials:

- PBT Polyester
- SS Stainless steel
- PP Polypropylene
- PE Polyethylene
- NR Nitrile rubber



TOP VIEW

